

6300 Components, Cables, and Light Posts

Transformer

28.1588.00



- For all 6300 dental lights after serial number D415121 (2004)

Dental Light Circuit Board

28.1577.00 Kit



- For 6300 wall-, track-, Preference-, and ceiling-mount dental lights after serial number D415121 (2004)
- Includes bracket and standoffs

Intensity Switch

43.0054.00



- For 6300 wall-, track-, Preference-, and ceiling-mount dental lights after serial number D415121 (2004)
- A-dec 571 light

Lubriplate

048.107.00










- Use on light hub
- 3/8 ounce tube

Track Cap

028.008.00



CABLE ASSEMBLIES	PART NUMBER	PRICE
Track light track and trolley, after April 1, 2004	28.1604.00	
Track light flexarm, after April 1, 2004	28.1584.00	
Wall and Preference mount, after April 1, 2004	28.1585.00	
Post mount, after April 1, 2004	28.1586.00	
Ceiling mount, after April 1, 2004	28.1587.00	
Dental light 216" (5486 mm), A-dec 571	28.1838.00	

LIGHT POSTS		PART NUMBER WHITE	PART NUMBER SURF	PRICE
	for Performer: 24.5" (622 mm) H for installation on cuspidor or assistant's instrumentation: includes post, adapter, trim ring, and power cord	28.1262.01	28.1262.00	
	for Performer: 42.25" (1,073 mm) H x 17" (432 mm) W for installation on Performer chair; with chair only	28.1263.01	28.1263.00	
	for Pre-Cascade chairs: 2" (51 mm) OD x 40" (1,016 mm) H for use with chair-mount to mount A-dec post-mount lights to pre-Cascade chairs	28.1976.00 -	- 28.1143.00	
	for 1040 Chair: 2" (51 mm) OD x 46" (1,168 mm) H x 25.25" (641 mm) W only needed for installing A-dec post-mount light to Cascade 1040 chair	-	28.1105.00	
	for 1021/1221 Chair: 2" (51 mm) OD x 46" (1,168 mm) H x 25.25" (641 mm) W only needed for installing A-dec post-mount light to Cascade 1040 chair	-	28.0881.01	
	for Cascade post box (extension kit): 2" (51 mm) OD x 32" (813 mm) H for post-mount light to Cascade post box: includes power cord, post, and hardware	28.1030.01	28.1030.00	
	for A-dec 361 support center: 2" (51 mm) OD x 32" (813 mm) H for installation on A-dec 361 support center	99.1136.00	-	